



# MIDMEKI™

## – Food X-Ray Inspection


The options for quality control in the food industry have long been limited. Until now there were only simple metal detectors on one hand and high-price X-ray systems on the other. With Mekitec, you finally have the choice.

### MIDMEKI™ – Offering the Best Value

MIDMEKI quality control system uses the latest X-ray image processing technology. With this system, we expand our unique product line with a system that combines the benefits of our compact MEKI™ with a wider conveyor and significantly larger detection area.

It is especially designed for the inspection of larger food products and trays of smaller products. High moisture, salt content or different type of packaging materials (like metal) are not a problem for the inspection.

MIDMEKI requires the least amount of installation space in the production line compared to any other comparable X-ray system. Like with MEKI™, with MIDMEKI we focus on what is important and necessary in an X-ray for a food producer, so we can deliver the best value to Mekitec's most valuable asset – our customer.




MIDMEKI™ is suitable for industries such as:



For more information, visit [www.mekitec.com](http://www.mekitec.com)



# X-Ray Inspection System for Larger Products



## TECHNICAL SPECIFICATIONS

Detection area	400 mm x 200 mm
Conveyor speed	min. 0.1 m/s max. 0.98 m/s
X-ray power	40-80 kV, 0.2-5.0 mA, max 200 W
X-ray leakage	less than 1 µSv/h
Detector	Linear scanner, resolution 0.4 mm
Software	Mekitec X-Ray Inspection System SW
Operating system	Windows 10
Connectivity	USB, Ethernet
HMI	12" Color TFT LCD Screen
Operation Temperature	0-35 °C ambient
Cooling	Optional air conditioner
IP rating	IP65
Relative humidity	30-85%, non-condensing
System power supply	110/240 VAC, 50-60 Hz
Dimensions (W x D x H)	1000/1400 mm x 702 mm x 2020 mm
Weight	220 kg
Material	Stainless steel, brushed
Reject options	Optional air reject or pusher with bins
System conveyor	EU and FDA food use approved conveyor belt
Radiation protection	EN 61010-02-091, FDA CFR 21 part 1020, 40
Safety switches	Safety circuit CAT 3, Performance Level PL d

## DETECTION AREA

Inspected product must fit completely inside the detection area.



MIDMEKI is especially suitable for the inspection of packaged products and trays with several products. For application with smaller products, please refer to the datasheet MEKI.

**Mekitec Oy, [info@mekitec.com](mailto:info@mekitec.com), [www.mekitec.com](http://www.mekitec.com)**

Disclaimer: All information is provided for information purposes only and shall not be considered as assured characteristics. The information and technical data presented in this document are subject to change. Customers should obtain and verify the latest relevant information before placing orders. If you have any questions related to the datasheet, please contact us via email or phone. Thank you. DS\_EN\_MIDMEKI\_052018A

**INTEKO Representations - Imports LTD**

75 Geraka Aven. | 15344 Gerakas | Greece | T: +30-210-8101196 | F: +30-210-8101279 | [info@inteko.gr](mailto:info@inteko.gr)